

Part number	Resolution
GF SENT TX DP-1.2	up to 4096 x 2160
GF SENT TX DP-1.1	up to 2560 x 1600, 2048 x 2048
GF SENT TX DP 1.0	up to 1920 x 1200

To add DisplayPort recording to an existing DVI recorder installation , use DisplayPort Split & Convert For Sentinel Recorders.

Figure 1 DisplayPort video

<b>Key</b> Yellow = End user Green = OEM Blue = Thruput	<b>Sentinel connection diagram</b> Copyright 2016 Thruput Limited DN 1343-0100 Issue: 8.3      Date: Dec 2016
--	--





Figure 2 DVI DL or SL video

**Key**  
Yellow = End user  
Green = OEM  
Blue = Thruput

**Sentinel connection diagram**  
Copyright 2016  
Thruput Limited  
DN 1343-0100 Issue: 8.3 Date: Dec 2016

**Thruput Limited**  
14-15 Londonderry Farm,  
Keynsham Road, Willsbridge,  
Bristol, BS30 6EL, United Kingdom

Office: +44 117 932 85 85  
Fax: +44 117 932 93 39  
Web: www.thruput.co.uk  
Email: sales@thruput.co.uk



**Part number**  
GF SENT TX DVI-I

**Resolution**  
up to 1600 x 1200

For High resolution analogue video, use the Sentinel RGB portal with the GF SENT TX DVI DL.

Figure 3 Analogue video

**Key**  
Yellow = End user  
Green = OEM  
Blue = Thruput

**Sentinel connection diagram**  
Copyright 2016  
Thruput Limited  
DN 1343-0100 Issue: 8.3 Date: Dec 2016